TULIP 200

特点

- 集光固化机及美白仪于一体
- 强大的光功率输出,最高可达1800mW/cm²
- 五种治疗模式:最强、中强、渐强、脉冲、渐转强脉冲
- 时间可设置:光固化时间(0~60s),美白时间 (0~30m)
- 彩色LCD显示
- 电池组合使用, 座充、直充两用, 即充电即用
- LED冷光輸出能治疗所有的牙齿组织
- 低电压报警功能

间歇工作(美白工作模式下,两次操作时间应相隔3分钟

以上)'' 技术参数

整机

大小: φ33mm

重量:250g

级别: Ordinary,B type,Intermittent working 工作电压: 100~240V(AC), 50~60HZ

模式: LED Curing Light+Whiten accelerator 5 working

mode (optional).

电池

类型: Lithium Battery

容量: 2200Mah

光学参数

波长: 420—490nm 光强: > 1200mW/cm² max reach 1800 mW/cm²

CHARACTERISTICS

- Unifies both whitening accelerator and LED curing light
- Strong optical output power, maximum to 1800mW/cm²
- Five treatment modes: Turbo, Normal, Soft start, Pulse, Pulse soft start
- Time setting: 0~60s for LED curing light, and 0~30 mins for whitening
- Full color LCD display
- Interchangeable battery pack, with both seat charger and direct charger
- LED cold light output can treat all dental tissue
- Alarm for low voltage
- Discontinuous operation: in the mode of whitening, the timegap should be over 3 mins between two operations

TECHNICAL PARAMETER

Unit

Size of host:: φ 33mm

Weight of host: 250g

Grading: Ordinary, B type, Intermittent working Working volt: 100~240V (AC), 50~60HZ

Working mode: LED Curing Light+Whiten accelerator, 5 working

mode (optional)

Battery

Type: Lithium Battery

Battery capacity: 2200Mah

Optics Parameter

Wave length: 420-490nm

Luminous intensity: > 1200mW/cm² , max reach 1800 mW/cm²





标准配件 Standard Accessories







